

Data Sheet LTX-D25.4-FMX

1" Concave TPX Lens



Table of Contents

Page

1	General.....	1
2	Specification and Application Note.....	2
3	Mounting Options.....	3
4	Complementary TPX Lenses.....	4
5	Contact Details.....	4

1 General

The concave TPX lenses with a diameter of 1" / 25.4 mm have been developed for the control of THz radiation.

Nomenclature

LTX-D25.4-FMX

LTX-D25.4-FMX	Type	Lens
LTX-D25.4-FMX	Material	TPX
LTX-D25.4-FMX	Form	Asphere / Sphere
LTX-D25.4-FMX	Diameter	25.4 mm
LTX-D25.4-FMX	Focal length	Var

Option:

LTX-D25.4-FX-MX	Mounting	Var
-----------------	----------	-----

2 Specification and Application Note

Table 1: Specification and Application Note of TPX lenses

Lens	LTA-D25.4-FM50	
Specification		
Material	TPX / Polymethylpentene	
Refractive index	1.47	
Form	Asphere	
Diameter [mm]	25.4 ± 0.1	
Thickness center [mm]	5.0 ± 0.05	
Thickness edge [mm]	7.6	
Application Note		
Focal length [mm]	- 50.0	
Clear aperture [mm]	21.0	
Aperture angle [°]	13.1	
NA	0.23	
Airy Disc	0.3 THz	5.25
	1.0 THz	1.57
	3.0 THz	0.52




Figure 1: Principal drawing of a convex TPX lens

Dia	Diameter
T _c	Thickness center
T _e	Thickness edge
FL	Focal length
CA	Clear Aperture
α	Aperture angle

3 Mounting Options

The TPX lenses are sold alone by default. But they can be ordered in a lens tube¹ with SM1 thread for easy mounting:

LTX-D25.4-FMX-M12.7	12.7 mm lens tube (length without external thread)
LTX-D25.4-FMX-M25.4	25.4 mm lens tube (length without external thread)

¹ Outer diameter: 30.5 mm; 1x Internal SM1 thread: 1x External SM1 thread

4 Complementary TPX Lenses

We are offering the following complementary TPX lenses:

LTX-D25.4-FX	1" Convex TPX Lens
LTX-D50-FX	2" Convex TPX Lens
LTX-D50-FMX	2" Concave TPX Lens

Please check their individual data sheets for further details.

5 Contact Details

BATOP GmbH
Stockholmer Straße 14
07747 Jena
Germany

E-Mail: info@batop.de (Sales)
thz@batop.de (Support)
Phone: +49 3641 634009 0
Fax: +49 3641 634009 20